



HIGH PERFORMANCE MATERIALS FOR MEDICAL TECHNOLOGY




» CONTENT


- » Our Company
- » **MEDIGEHR®** General Information
- » **MEDIGEHR®** Products
- » **MEDIGEHR®** Applications
- » Sterilization / Cleaning
- » **MEDIGEHR®** Delivery Programme
- » Contact



» FAMILY OWNED AND OPERATED COMPANY WITH TRADITION SINCE 1932



Eduard Gehr




Werner Gehr



Annette and Helmut Gehr



» GEHR – AN INTERNATIONAL COMPANY



» US headquarters and production site
Philadelphia, PA, USA



» World headquarters and production site
Mannheim, Germany




» Asia headquarters and warehouse
Hong Kong

» QUALITY AND INNOVATION




» OUR COMPETENCES

STOCK SHAPES





CUSTOMER SOLUTIONS



» GEHR EXPERTISE

**EXTRUDED RODS, SHEETS, TUBES,
PROFILES AND FILAMENTS**

- » Rods up to 700 mm diameter
- » Thick plates up to 300 mm thickness
- » Calendered sheets from 1 mm
- » Decorative precision tubes
- » Semi-finished products for medical applications
- » Filaments for professional 3D printing



» ENVIRONMENTAL PROTECTION AND SUSTAINABILITY

CO₂-NEUTRAL PRODUCTION

- Conversion to green electricity and green gas in Mannheim and Philadelphia.
- Achievement of the implementation packages of Katowice Scope1 and Katowice Scope1 and 2

SINCE 2016: 100% RENEWABLE ELECTRICITY

Since 2016, total electricity requirements covered by renewable energies - mainly from hydropower in Norway.

COOLING PROCESS OPTIMIZED


In order to sustainably conserve water as a resource, we have also made mechanical adjustments to our plants. This has enabled us to significantly reduce the amount of water required in the cooling system as well as the supply of fresh water.

RECYCLING CONCEPT FOR THE AVOIDANCE OF PRODUCTION WASTE

The returned material is sorted, ground, recycled and reused in production wherever possible and permitted.



ECOGEHR®



» SUSTAINABILITY REPORT 2024

CERTIFICATIONS

- » ISO 9001, ISO 13485, ISO 14001, ISO 50001, ISO 45001
- » ISCC Plus
- » ECOVADIS Rating 2024: Silver



CORPORATE PHILOSOPHY

- » Long-term independence
- » Extensive sustainable portfolio
- » Quality leadership
- » Innovation
- » Corporate social responsibility in terms of sustainable management, CSR responsibility

REDUCTION OF ENERGY CONSUMPTION

Since 2013 10% reduction of energy per kg extruded material thru:

- » new efficient extruders
- » optimized annealing processes
- » new compressed air systems
- » energetic refurbishment of buildings
- » new photovoltaic system to be installed in 2023 that will cover approx. 15% of demand

SOCIAL RESPONSIBILITY

- » Below industry average for „1000-man quota“ (accident rate per 1000 full-time workers)
- » Cooperation with the University of Mannheim
- » Flexible working hours / mobile working stations
- » Sponsoring local sport events / teams

RECYCLING

- » Recycling rate increased to 7,8%
- » Reduced scrap rate by 2%
- » Strategic partnership with plastic recovery company

LIFECYCLE ASSESSMENT

- » Status Quo carbon footprint analysis based on GHG protocol
- » Currently emissions are 2145t CO₂ eq.

GREENHOUSE GAS EMISSIONS

- » Scope 1: 7% Scope 2: 1% Scope 3: 92%
- » **Reduction of 30% in 2024** (compared to 2023)

ACCOMPLISHED ACTIONS

- » **ECOGEHR®** & **ECO FIL-A-GEHR®**
- » Since 2016: green electricity
- » Since 2020: green gas
- » ECOVADIS Rating 2022/2023/2024: Silver
- » ISCC+ biocircular PP for writing instruments
- » Member of Mannheim climate protection alliance

CORPORATE GOVERNANCE

- » Corporate Environment, culture, leadership
- » Dealing with business partners, customers, suppliers
- » Supply chains
- » Anti Trust, compliance, confidentiality
- » Whistleblowing

» GENERAL INFORMATION ABOUT MEDIGEHR®

Products suitable for medical and pharmaceutical applications with direct body contact with tissue, bone, skin and mucosa for up to 24 hours. All raw materials used for the medical grade products are food grade (FDA, EU 1245/2020) and have been tested and evaluated by an independent accredited testing laboratory and meet the following biocompatibility requirements:

- » ISO 10993-1: Assessment and testing as part of a risk management system
- » ISO 10993-5: Tests for in vitro cytotoxicity
- » ISO 10993-12: Sample preparation and reference materials
- » ISO 10993-18: Chemical characterization of materials*
- » USP Class VI*



» GENERAL INFORMATION ABOUT **MEDI-GEHR**®

During production, we ultrasonically inspect our semi-finished products to ensure that they are free of defects and voids. As a manufacturer, we thus fulfill a special duty of care that makes it easier for medical device manufacturers to obtain approval for their end products by reducing costs and time. We also attach great importance to the traceability of the stock goods that leave our production facilities.



» MEDIGEHR® PP-HT MG

- » High heat resistance
- » High stiffness
- » High surface hardness
- » Low density
- » Very high chemical resistance
- » Resistance to hot steam sterilization
- » Brittle at low temperature

APPLICATIONS:

- » Sterilization cassettes and inserts
- » Centrifuge holders
- » Analysis technology





» MEDIGEHR® PET MG

- » Very good chemical resistance
- » Very high impact strength
- » High surface hardness
- » High hydrolysis resistance
- » High creep resistance
- » Good polishability
- » Good sliding friction properties and abrasion resistance
- » Good electrical insulation properties
- » High resistance to gamma radiation

APPLICATIONS:

- » Operating room lights
- » Housings
- » Medical components
- » Disposables for biomedical applications



» MEDIGEHR® PC MG

- » Continuous service temperature from -60°C to $+120^{\circ}\text{C}$
- » Very high stiffness
- » Very high impact strength
- » Very high dimensional stability
- » Resistance to x-ray irradiation
- » Very good heat deflection temperature (approx. 135°C)
- » High surface hardness

APPLICATIONS:

- » Surgical lights
- » Dialysis machines
- » Incubators
- » Oxygen equipment
- » Inhalers





» MEDIGEHR® PEI MG

- » Long-term Service Temperature 170°C
- » High Chemical and Hydrolysis Resistance
- » Very high strength and stiffness as well as creep resistance
- » Very high torsional strength and hardness
- » High heat resistance
- » Very Good Weather Resistance
- » High resistance to γ -rays

APPLICATIONS:


- » Delivery capsule for minimally invasive procedures
- » Autoclave components
- » Structural medical components
- » Radiation therapy systems
- » Infusion pumps

» MEDIGEHR® PPSU MG

- » Continuous service temperature 170°C
- » High strength and stiffness
- » Very high toughness (even at low temperatures)
- » Very high dimensional stability
- » Very high chemical resistance
- » Very good sterilizability
- » Lower chemical resistance than comparable semi-crystalline materials

APPLICATIONS:

- » Instrument handles
- » Instruments for microinvasive surgery
- » Components in the food industry
- » Pump impellers, pump bodies
- » Valves



» MEDIGEHR® PPSU MG



» Your benefit: All dimensions are made-to-order; customization with fast delivery and minimum order quantity of 25 kg

» Available colors:

red (~RAL 3001)

blue (~RAL 5005)

yellow (~RAL 1006)

green (~RAL 6026)

purple (~RAL 4005)

» More colors are available on request

» Material: Synsco Radel® PPSU


» Diameter Ranging: 10 to 100mm

APPLICATIONS:

» Instrument handles

» Sizers and spacers

» Surgical instruments



» MEDIGEHR® PEEK MG

- » Continuous service temperature -40°C to +260°C
- » Excellent sterilizability with all common methods (superheated steam, gamma, e-beam, EtO)
- » Very high strength, stiffness and toughness
- » Very high temperature and heat resistance
- » Very high creep resistance
- » Very high dimensional stability
- » Very high resistance to β -, γ -, X-ray and infrared radiation
- » High resistance to hydrolysis
- » Good wear properties
- » Low water absorption
- » Inert


Raw material:


- » Synsqo® KETASPIRE® KT820
- » Victrex® 450G

» MEDIGEHR® PEEK MG

APPLICATIONS:

- » Dental instruments
- » In-vitro diagnostics
- » Locking devices
- » Connectors
- » Sealing rings, spacers, dosing systems
- » Flanges and sleeves, housing parts
- » Grippers, holders, insulation sleeves,
- » Primary packaging in the pharmaceutical sector





» MEDIGEHR® PEEK MG

» Your benefit: All dimensions are made-to-order; customization with fast delivery and minimum order quantity of 25 kg

» Available colors:

red (~RAL 3001)

blue (~RAL 5005)

yellow (~RAL 1006)

green (~RAL 6026)

purple (~RAL 4005)

» More colors are available on request

» Material: Solvay Ketaspire® KT-820

» Diameter Ranging: 10 to 100mm

APPLICATIONS:

» Dental instruments

» Sizer and spacer

» Locking devices



» **MEDI FIL-A-GEHR®**

MEDI FIL-A-GEHR® products are suitable for medical and pharmaceutical applications with direct body contact with tissue, bone, skin and mucosa for up to 24 hours. All materials meet the same requirements as the semi-finished products. Especially for our certificates and approvals:

FDA*, EU 10/2011*, ISO 10993-1, -5, -12, -18 and USP Class VI

* only for raw material

MATERIALS:

- » **MEDI FIL-A-GEHR®** PET MG (white and transparent)*
- » **MEDI FIL-A-GEHR®** PC MG
- » **MEDI FIL-A-GEHR®** PPSU MG
- » **MEDI FIL-A-GEHR®** PEEK MG



MEDI FIL-A-GEHR® PPSU MG
Arthroscope prototype



MEDI FIL-A-GEHR® PEEK MG
Instrument holder prototype



colored PEEK rods




colored PPSU tubes

» GEHR CUSTOMIZING

- » Special manufacture of semi finished products such as tubes, plates, rods, profiles, etc. for industrial and medical applications
- » Tolling of high performance material filaments (also for implants)
- » Extrusion of sheets and rods for medical and electronic segment in clean room
- » Extrusion of multi-layer co-extruded tubes




3-layer co-extruded tubes



1. layer

2. layer

3. layer



PPSU tubes for surgical instruments

» MEDIGEHR® meets ECOGEHR®

- » Started as a customer project
- » Application: Suction tube

Requirements:

- » Biobased or recycled material
- » All medical approvals
- » Transparent tube



Our solution:

- » ECO MEDIGEHR® PP Tubes
- » Material: PPH made of used cooking oil
- » Approvals on the raw material:
 - » ISO 10993
 - » USP <88> Class VI
 - » Food Contact: EU 10/2011, FDA 177.1520

» MEDIGEHR® APPLICATIONS




Dental Applications



Surgical Equipment



Surgical Instruments



Medical Disposables

» STERILIZATION / CLEANING

Product	UV irradiation	Gamma irradiation	Autoclave	Ethylene oxide	Hydrogene peroxide
MEDI GEHR® PP-HT MG	-	o	+	o	o
MEDI GEHR® PET MG	+	+	-	+	+
MEDI GEHR® PC MG	+	+	+	+	+
MEDI GEHR® PEI MG	+	+	+	+	+
MEDI GEHR® PPSU MG	-	+	+	+	+
MEDI GEHR® PEEK MG	-	+	+	+	+
MEDI FIL-A-GEHR® PET MG	+	+	-	+	+
MEDI FIL-A-GEHR® PC MG	+	+	+	+	+
MEDI FIL-A-GEHR® PPSU MG	-	+	+	+	+
MEDI FIL-A-GEHR® PEEK MG	-	+	+	+	+



*Discoloration may occur

+	Compatible
-	Incompatible
o	Not tested

» APPROVALS

Product	EU1245/2020	FDA	ISO10993-5	ISO10993-18	USP Class VI
MEDIGEHR® PP-HT MG	○	◐	●	●	●
MEDIGEHR® PET MG	◐	◐	◐	○	○
MEDIGEHR® PC MG	◐	◐	●	●	●
MEDIGEHR® PEI MG	◐	◐	●	○	○
MEDIGEHR® PPSU MG	◐	◐	●*	●*	●*
MEDIGEHR® PEEK MG	◐	◐	●*	●*	●*
MEDI FIL-A-GEHR® PET MG	◐	◐	◐	○	○
MEDI FIL-A-GEHR® PC MG	◐	◐	●	●	●
MEDI FIL-A-GEHR® PPSU MG	◐	◐	●	●	●
MEDI FIL-A-GEHR® PEEK MG	◐	◐	●	●	●



Not tested, but on request possible



Approvals on semi-finished products upon first delivery



Approvals on the raw material



Approvals on the semi-finished product


*

With limits (depending on the color and raw material)



VOLLSTÄBE / ROUND RODS

Ø mm	MEDI-GEHR PEEK MG®	MEDI-GEHR PPSU MG®	MEDI-GEHR PP-HT MG®	MEDI-GEHR PC MG®	MEDI-GEHR PET MG®
	Länge / Length: 1 2 3 m kg/m				
5	0,032	0,027			
6	0,040	0,038			
8	0,072	0,068			
10	0,110	0,106			0,097
12	0,164 ⊙	0,153		0,143	0,140
15	0,252	0,239		0,223	0,219
16	0,285 ⊙●	0,272		0,253	0,249
18	0,360	0,345		0,321	0,315
20	0,439 ⊙●	0,443 ●●●●●●		0,396	0,389
22	0,535	0,515		0,479	0,471
25	0,685 ⊙●	0,665 ●●●●●●	0,484 ⊙	0,619	0,608
28	0,850	0,834		0,776	0,763
30	1,000	0,985		0,891	0,876
32	1,110 ⊙●	1,089 ●●●●●●		1,013	0,996
36	1,430 ⊙●	1,379		1,283	1,261
40	1,740	1,750 ●●●●●●	1,230 ⊙	1,583	1,557
45	2,220	2,154		2,004	1,971
50	2,770 ⊙●	2,730 ●●●●●●	1,930 ⊙	2,474 ⊙	2,433
56	3,400	3,336			3,052 ⊙○
60	3,920 ⊙●	3,940	2,770 ⊙		3,503
65	4,550	4,495			4,111
70	5,400	5,213			4,768
75	6,100	5,984			5,474
80	6,960	6,970			6,228
90	8,800	8,617			7,882
100	10,800	10,900			9,731
110	13,000				
120	15,610				
125	16,930				
140	21,300				
150	24,600		21,472 ⊙		



PLATTEN / SHEETS

Länge / Length: 1 | 2 | 3 m

mm	Toleranzen / Tolerances mm		MEDI-GEHR PEEK MG®	MEDI-GEHR PPSU MG®	MEDI-GEHR PP-HT MG®	MEDI-GEHR PC MG®	MEDI-GEHR PET MG®
	min.	max.	Breite/Width 620 mm kg/m	Breite/Width 620 mm kg/m	Breite/Width 610 mm kg/m	Breite/Width 620 mm kg/m	Breite/Width 620 mm kg/m
15	+ 0,3	+ 1,5			8,743 ⊙	11,718	11,337
16	+ 0,3	+ 1,5	14,340 ⊙●			12,499	12,093
20	+ 0,3	+ 1,5	17,730 ⊙●	17,970 ●	11,657 ⊙	15,624 ⊙	15,116 ⊙○
25	+ 0,3	+ 1,5	22,320 ⊙●	22,270 ●		19,530	18,895
30	+ 0,5	+ 2,5			17,485 ⊙	23,436	22,674
35	+ 0,5	+ 2,5		31,390 ●		27,342	26,453
40	+ 0,5	+ 2,5	35,200 ⊙	35,690 ●	23,314 ⊙	31,248	30,232
50	+ 0,5	+ 2,5		44,290 ●		39,060	37,790



FILAMENTE / FILAMENTS

kg	MEDI-FIL-A-GEHR PEEK MG®	MEDI-FIL-A-GEHR PPSU MG®	MEDI-FIL-A-GEHR PC MG®	MEDI-FIL-A-GEHR PET MG®
	Ø 1,75mm	Ø 1,75mm	Ø 1,75mm Ø 2,85mm	Ø 1,75mm Ø 2,85mm
0,1	⊙	●		
0,2	⊙	●		
0,5	⊙	●		
1	⊙	●	⊙	⊙○

Auf Lager

Stock item

Farben / Colours:

- ⊙ natur / natural
 - ⊙ transparent / transparent
 - grün / green (~RAL 3262)
 - schwarz / black (~RAL 9004)
 - rot / red (~RAL 3000)
 - gelb / yellow (~RAL 1006)
 - blau / blue (~RAL 5005)
 - weiß / white (~RAL 9010)
 - lila / purple (~RAL 7668 C)
- Mehr Farben auf Anfrage / More colors on request

CONTACT US

GEHR GmbH

Casterfeldstraße 172, 68219 Mannheim, Germany
Tel.: +49 621 8789 - 0, info@gehr.de,
www.gehr.de

Mr. Dr. Giorgio Müller

Sales and Marketing Director
Tel.: +49 621 8789 - 194
Mail: mueller@gehr.de

Mr. Achim Hodapp

Sales Manager D/A/CH
Tel.: +49 621 8789 - 130
Mail: hodapp@gehr.de

Mr. Dirk Nüssgen

Senior International Sales Manager
Tel.: +49 621 8789 - 133
Mail: nuessgen@gehr.de

GEHR Plastics, Inc.

24 Creek Circle Boothwyn, PA 19061, USA
Tel.: +1 610 497-8941, info@gehrplastics.com,
www.gehrplastics.com

Mr. Bill Weaver

Director, Technical Services
Tel.: +1 484 768-6854
Mail: bweaver@gehrplastics.com

GEHR Plastics Italia

Dipro, Via Alessandria 55, 10152 Torino, Italy
Tel.: +33 011 24-89507, info@gehr.it,
www.gehr.it

Mr. Guido Nicol

Sales Manager Italy
Tel.: +33 011 24-89507
Mail: guido.nicol@dipro.it

GEHR Plastics Hong Kong Limited

Pak Sha Tsuen, Yuen Long
Tel.: +852 2690-1007, info@gehr.hk,
www.gehr.hk

Mr. YK Wong

CEO Asia / Pacific
Tel.: +65 96772991
Mail: yk.wong@gehr.de